www.iscwales.com

RP227 STRYDER Foot Ascender

Data Sheet


STRYDERtm



Boot shown for illustration purposes only



STRYDERtm utilises the same unique Stainless Steel cam used in our Hand Ascender. The coned cam-face allows positive engagement on the rope for a firm and reliable grip, with minimal wear to the sheath.





The foot-lever can be used to open/close the cam, with the other foot. The foot-lever can also be hooked over the body of the device (see photo to right), to hold the cam in the open (disengaged) position.

Should the user prefer, the foot-lever bar can be removed, by unscrewing an Allen screw. Removing the foot-bar allows greater pivot range of the cam. This in turn allows the user to deliberately remove the rope from the device, by using a kick technique with only the leg that the device is mounted on.

ISolutions in Metal

During the design & development of the STRYDERtm, durability and functionality were at the top of the priority list! The STRYDERtm utilises tried & tested geometry, to provide a smooth upward movement and positive engagement on the rope.

STRYDERtm is fully adjustable on both the horizontal and vertical straps, allowing the user to position the device on the boot, according to preference. The straps and protective under-foot sleeve are made from a specifically developed webbing, which has passed extensive abrasion testing.

The combination of the creep-free webbing and the mounting slot design, means that the device should remain firmly in position throughout use. The main strap is tightened by pulling firmly on the strap and is released by pulling upwards on the toggle, in a one-handed action.

Dimensions (Width, Height, Thickness)	75, 52, 25mm / (3, 2, 1")
Weight (complete with strap)	198g (7oz)
Rope Size	8-13mm (5/16/ 1/2")
Material	Aluminium (Anodised)
MBS	2.5kN (562lbf)
WLL	140kg (308lb)

Serial Numbered as standard

NOT for PPE

climb. work. rescue